

INCUBATOR

i25

axyos

| | |
|---|---|
| Capacity (litre) | 25 |
| Exterior [Stainless Steel Facia] (high x wide x deep mm) | 620 x 370 x 420 |
| Interior [Stainless Steel] (high x wide x deep mm) | 295 x 262 x 300 |
| Shelf size (wide x deep mm) | 260 x 280 |
| Shelves | 2 |
| Shelf positions | 3 |
| Shelf Space (mm) | 65 |
| Fan circulation | Optional |
| Heating (stainless sheathed element) | 0.25kW |
| Micro-Digital control (with digital readout and LCD) | Included |
| Temperature range | Ambient +5°C to 80°C (other ranges available) |
| Temperature accuracy | ±0.1°C at sensor chamber typically ± 0.5°C |
| Electrical | 220-240v , 50-60Hz single phase (alternative power ranges available) |



Options Description

| | |
|------|---|
| ac | °C alarm - Audible & visual for ±°C tolerances |
| ad | Door open alarm - audible & visual |
| c | Four Swivel Castors - Two lockable |
| cr | Circular 7 day or 24 hr chart recorder for °C (pls call for other parameters/types) |
| cn | Fan circulation for increased spatial accuracy & °C response |
| f | Adjustable feet (cannot be installed if w selected) |
| v | Internal power supply for shaker or other similar appliance |
| vo | Door switch to deactivate internal power supply eg: turn off orbital shaker |
| s? | Extra Shelves |
| tp?? | Sealed test hole installed in chamber for test cables (advise diameter in mm) |
| tc | Countdown to stop timer |
| to | Auto programmable start stop timer |
| id | Internal perspex viewing door |
| ct | Certificate of calibration and °C/time graph of test against Australian NATA traceable device |

